RUBBER VOLTAGE GLOVES



Class 00

Standards:

NFPA 70E-2018 Max Use Voltage 500V AC/750V DC ANSI/ASTM D120 Class 00, Type 1

Sizes 8-12



Class 0

Standards:

NFPA 70E-2018 Max Use Voltage 1000V AC/1500V DC ANSI/ASTM D120 Class 0, Type 1

Sizes 8-12



Class 2

Standards:

NFPA 70E-2018 for Arc Flash Max Use Voltage 17000V AC/25500 V DC ANSI/ASTM D120 Class 2, Type 1

Sizes 8-12



122 West 22nd Street Oak Brook, IL 60523 P 866.680.4950







ENESPRO PPE VOLTAGE RATED RUBBER GLOVES

Rubber voltage rated gloves and leather protectors are the most common personal protective equipment (PPE) used for shock protection. The rubber gloves must be certified to ensure that they can withstand the voltages for which they are rated to provide, and they must be put into use within 12 months of the test stamped on the front of the glove. Once gloves are issued for use, they must be retested or replaced within 6 months of the date they were put into use. This cycle is continued for the life of the glove.

In addition, the gloves must be air-tested and visually inspected for damage and adequacy immediately before each use. It is a requirement to always wear leather protectors and to follow the user instruction guide provided with each glove.

For additional information, please refer to ASTM F496.

It is important to note that workers must also be trained in the proper use, care, and storage of rubber gloves and leather protectors.

| Class | Tag Color | Proof Test Voltage AC/DC | Maximum Use Voltage AC/DC |
|-------|-----------|-----------------------------|------------------------------|
| 00 | Beige | 2,500 / 10,000 | 500 / 750 |
| 0 | Red | 5,000 / 20,000 | 1,000 / 1,500 |
| 1 | White | 10,000 / 40,000 | 7,500 / 11,250 |
| 2 | Yellow | 20,000 / 50,000 | 17,000 / 25,500 |
| 3 | Green | 30,000 / 60,000 | 26,500 / 39,750 |
| 4 | Orange | 40,000 / 70,000 | 36,000 / 54,000 |

ENESPRO PPE GLOVE KITS

All Enespro PPE glove kits come complete with:

- · Rubber Voltage Rated Gloves
- · Leather Protectors
- · Canvas Carry Bag



SIZING & STORAGE

FOR RUBBER VOLTAGE GLOVES

Selecting the Correct Size

Enespro® offers Rubber Voltage Gloves in sizes ranging from 8 to 12. To make sure you are ordering the correct glove size, measure the circumference around your palm (see illustration). If you are in between sizes, we recommend ordering the larger size.

The Correct Way to Store Your Gloves


To ensure gloves are safely stored:

- · Keep out of high heat areas
- · Avoid high moisture areas
- · Don't place in direct sunlight
- · Keep out of contact with any chemical substance
- · Store them flat
- · Do not fold the gloves

IMPORTANT INFORMATION

TESTING AND RETESTING

- · Gloves must be put into use within one year of test date
- · If one year has passed since the gloves have been tested and they have not been open, they must be sent back for retesting
- · Once gloves are issued for use, they must be retested or replaced within 6 months from the date they were distributed to employees.
- · For additional information, refer to ASTM F496



ELECTRICAL SAFETY PPE TRANSFORMED enesproppe.com